



B33F244NW Flexible Copper Braid

By Burndy
Catalog # [B33F244NW](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Length	24 in
Dimension - L Length Overall	610 mm
mm	
Height	0.62 in
Width	3 in
Dimension - Hole Size	0.56 in
inch	
Dimension - Length Overall	24 in
inch	
Thickness - Pad	0.63 in
Dimensions	24 in x 3 in x 0.62 in

General

UPC	781810658765
Material	Copper
UPC 14 Digit GTIN	00781810658765

Logistics

Minimum Pack Quantity	1
Pallet Quantity	120
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)