



B33F24N Flexible Copper Braid

By Burndy
Catalog # [B33F24N](#)

Flexible Tinned Copper Braid 24 X 3 X 0.62.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B33F24N
Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	9
UPC	781810551066
UPC 14 Digit GTIN	00781810551066

Dimensions

Dimension - L Length Overall	610
mm	
Dimension - Length Overall	24
inch	
Dimension - Width inch	3
Dimension - Width mm	76 mm
Length	24 in

Electrical Ratings

Amperage Rating	2000 A
-----------------	--------

Certifications And Compliance

Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	540

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50005747](#)
[Specifications - B33F24N](#)



A Hubbell brand