



# B33G394NTN Flexible Copper Braid

By Burndy  
Catalog # B33G394NTN

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

Standards - RoHS Compliance    CM  
Status

## Configuration

Connector Type                      Braid

## Current

Rating - Indoor Amperage            2500  
Rating - Outdoor Amperage        3000

## Dimensions

Length                                    39 in  
Dimension - L Length Overall       991 mm  
Dimension - Length Overall        39.00 in  
inch

## General

Plated                                    Y  
Material - Ferrules                   Y  
Physical Attribute - Number of    3  
Braids  
UPC                                        781810427309  
Material                                  Copper  
UPC 12 Digit                            781810427309  
UPC 14 Digit GTIN                    00781810427309

## Logistics

Minimum Pack Quantity            1

## Product Assets

[Catalog \[English\]](#)