



B34G15TNCG1 Flexible Copper Braid

By Burndy
Catalog # B34G15TNCG1

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance CM
Status

Configuration

Connector Type Braid

Current

Rating - Indoor Amperage 3000
Rating - Outdoor Amperage 3600

Dimensions

Length 15 in
Dimension - L Length Overall 381 mm
Dimension - Length Overall 15.00 in

General

Plated Y
Material - Ferrules Y
Physical Attribute - Number of 12
Braids
UPC 781810427248
Material Copper
UPC 12 Digit 781810427248
UPC 14 Digit GTIN 00781810427248

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalog \[English\]](#)