



B3B067L10D75G1W Flexible Copper Braid

By Burndy
Catalog # B3B067L10D75G1W

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Package Height	0.000 in
Length	10.75 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	621945451506
Material	Copper
UPC 12 Digit	621945451506
UPC 14 Digit GTIN	00621945451506

Logistics

Minimum Pack Quantity	3
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)