



B3E12 Flexible Copper Braid

By Burndy
Catalog # B3E12

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	700
Rating - Outdoor Amperage	840

Dimensions

Dimension - Pad Width inch	1.64 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	305 mm
Dimension - Hole Size inch	0.44 in
Length	12 in
Dimension - D inch	3.00 in
Dimension - N inch	0.75 in
Dimension - Length Overall inch	12.00 in

General

Material - Ferrules	Y
Plated	Y
Physical Attribute - Number of Braids	3
UPC	781810004920
Material	Copper
UPC 12 Digit	781810004920
UPC 14 Digit GTIN	00781810004920

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)