



B3E24N Flexible Copper Braid

By Burndy
Catalog # B3E24N

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

General

Catalog Number	B3E24N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	Y
Plating Type	Unplated
UPC	781810048160
UPC 14 Digit GTIN	00781810048160

Dimensions

Dimension - D inch	3 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.64 in
Dimension - Z (inch)	3.25 in
Length	24 in
Thickness	0.31 in

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	6
Pallet Quantity	540

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B3E24N](#)



A Hubbell brand