



B3F12D50NTN Flexible Copper Braid

By Burndy
Catalog # B3F12D50NTN

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance CM
Status

Configuration

Connector Type Braid

Current

Rating - Indoor Amperage 820
Rating - Outdoor Amperage 980

Dimensions

Package Height	0.000 in
Length	12.5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	318 mm
mm	
Dimension - Length Overall	12.50 in
inch	

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
UPC	781810478547
Material	Copper
UPC 14 Digit GTIN	00781810478547

Logistics

Minimum Pack Quantity	128
Pallet Quantity	1350
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)