



B3F17N Flexible Copper Braid

By Burndy
Catalog # B3F17N

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	820
Rating - Outdoor Amperage	980

Dimensions

Package Height	0.000 in
Length	17 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	432 mm
mm	
Dimension - Length Overall	17.00 in
inch	

General

Plated	N
Material - Ferrules	Y
Physical Attribute - Number of	3
Braids	
UPC	781810235102
Material	Copper
UPC 14 Digit GTIN	00781810235102

Product Assets

[Catalog \[English\]](#)