



BURNDY

B3F18HQ Flexible Copper Braid

By Burndy
Catalog # [B3F18HQ](#)
Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Certification - ETL

No
Certification - UL Recognized
No
Standards - RoHS Compliance Status
CM
Certification - cULus
No
UL Listed
Yes
Certification - CSA Approved
No

Configuration

Connector Type
Braid

Dimensions

Dimension - Pad Width inch
1.44 in
Package Height
0.000 in
Length
18 in
Thickness
0.56 in
Package Weight
0.000 lb.
Package Length
0.000 in
Package Width
0.000 in
Dimension - L Length Overall mm
457 mm
Dimension - Hole Size inch
0.56 in
Dimension - Length Overall inch
18.00 in

General

Plated
Y
Material - Ferrules
Y
Physical Attribute - Number of Braids
3
UPC
781810459317
Material
Copper
UPC 12 Digit
781810459317
UPC 14 Digit GTIN
00781810459317

Logistics

Minimum Pack Quantity
1

Product Assets

[Catalog.\[English\]](#)



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRDY-B3F18HQ-SPEC-EN | REV 5/2026