



B3F25 Flexible Copper Braid

By Burndy
Catalog # B3F25

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B3F25
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	N
UPC	781810432259
UPC 14 Digit GTIN	00781810432259

Dimensions

Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	635 mm
Dimension - Length Overall inch	25.00 in
Dimension - Pad Width inch	1.44 in
Dimension - Z (inch)	3.25 in
Length	25 in
Thickness	0.56 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	15
Pallet Quantity	1350

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - B3F25 Specification Sheet French](#)
- [Specifications - B3F25 Specification Sheet English](#)



A Hubbell brand