



B3G14N Flexible Copper Braid

By Burndy
Catalog # B3G14N

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	960 A
Rating - Outdoor Amperage	1150 A

Dimensions

Length	14 in
Dimension - L Length Overall mm	356
Dimension - Length Overall inch	14.00

General

Plated	Y
Material - Ferrules	Copper
Physical Attribute - Number of Braids	3
UPC	781810529812
Material	Copper
UPC 14 Digit GTIN	00781810529812

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)