



B41D24D02G3 Flexible Copper Braid

By Burndy
Catalog # [B41D24D02G3](#)

Flexible Copper Braid.

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B41D24D02G3
Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	4
Plated	Y



UPC 621945464643

Dimensions

Dimension - L Length Overall	610
mm	
Dimension - Length Overall	24.02
inch	
Length	24.02 in

Certifications And Compliance

Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	600

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50071285](#)
- [Specifications - B41D24D02G3](#)



A Hubbell brand