



B42E144N Flexible Copper Braid

By Burndy
Catalog # [B42E144N](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
Dimensions	
Length	14 in
Dimension - L Length Overall mm	356 mm
Height	0.38 in
Width	4 in
Dimension - Length Overall inch	14.00 in
Dimensions	14 in x 4 in x 0.38 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	8
UPC	781810294772
Material	Copper
UPC 14 Digit GTIN	00781810294772

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)