



B42G164NTN Copper Braid

16"x4.00"x0.69"

By Burndy
Catalog # [B42G164NTN](#)

Copper Braid 16"x4.00"x0.69"



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance EX
Status

Configuration

Connector Type Braid

Dimensions

Dimension - Pad Width inch 4.00 in
Length 16 in

Thickness	0.69 in
Dimension - L Length Overall mm	406 mm
Height	0.69 in
Width	4 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	16.00 in
Dimensions	16 in x 4 in x 0.69 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	8
UPC	781810375570
Material	Copper
Plating Type	Tin Plated
UPC 12 Digit	781810375570
UPC 14 Digit GTIN	00781810375570

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)