



B4D14N Flexible Copper Braid

By Burndy
Catalog # B4D14N

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	600
Rating - Outdoor Amperage	720

Dimensions

Length	14 in
Dimension - L Length Overall	356 mm
mm	
Height	0.32 in
Width	1.19 in
Dimension - Length Overall	14.00 in
in	
Dimensions	14 in x 1.19 in x 0.32 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of	4
Braids	
UPC	781810200056
Material	Copper
UPC 14 Digit GTIN	00781810200056

Logistics

Pallet Quantity	1200
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)