



B4D18 Tinned Copper Braid 18"x1.19"x0.34"

By Burndy
Catalog # B4D18

Tinned Copper Braid 18"x1.19"x0.34"



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Dimension - Pad Width inch	1.19 in
Package Height	0.000 in

Length	18 in
Thickness	0.32 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	457 mm
Height	0.34 in
Width	1.19 in
Dimension - Hole Size inch	0.44 in
Dimension - Length Overall inch	18.00 in
Dimensions	18 in x 1.19 in x 0.34 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
UPC	781810078280
Material	Copper
Plating Type	Tin Plated
UPC 12 Digit	781810078280
UPC 14 Digit GTIN	00781810078280

Logistics

Minimum Pack Quantity	25
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)