



B4D24 Flexible Copper Braid

By Burndy
Catalog # B4D24

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	600 A
-----------------	-------

Dimensions

Package Height	0.000 in
Length	24 in
Package Weight	0.000 lb.
Dimension - Width inch	1.18
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	610 mm
Height	0.34 in
Width	1.18 in
Dimension - Length Overall inch	24
Dimensions	24 in x 1.18 in x 0.34 in

General

Plated	N
Material - Ferrules	Copper
Physical Attribute - Number of Braids	4
UPC	781810088845
Material	Copper
UPC 12 Digit	781810088845
UPC 14 Digit GTIN	00781810088845

Logistics

Minimum Pack Quantity	3
-----------------------	---

Product Assets

[Catalog \[English\]](#)