



B4D25 Tinned Copper Braid

25"x1.19"x0.32"

By Burndy
Catalog # [B4D25](#)

Tinned Copper Braid 25"x1.19"x0.32"



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Dimension - Pad Width inch	1.19 in
Length	25 in
Thickness	0.32 in
Dimension - L Length Overall mm	635 mm
Height	0.32 in
Width	1.9 in
Dimension - Length Overall inch	25.00 in
Dimensions	25 in x 1.9 in x 0.32 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
UPC	781810201589
Material	Copper
Plating Type	Tin Plated
UPC 12 Digit	781810201589
UPC 14 Digit GTIN	00781810201589

Logistics

Minimum Pack Quantity	1
Pallet Quantity	90
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)