



B4D72 Tinned Copper Braid 72"x1.19"x0.32"

By Burndy
Catalog # B4D72

Tinned Copper Braid 72"x1.19"x0.32"



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Dimension - Pad Width inch	1.19 in
Length	72 in
Thickness	0.32 in
Dimension - L Length Overall mm	1829 mm
Height	0.32 in
Width	1.19 in
Dimension - Hole Size inch	0.44 in
Dimension - Length Overall inch	72.00 in
Dimensions	72 in x 1.19 in x 0.32 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
UPC	781810202074
Material	Copper
Plating Type	Tin Plated
UPC 12 Digit	781810202074
UPC 14 Digit GTIN	00781810202074

Logistics

Minimum Pack Quantity	1
Pallet Quantity	180
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)