



B4E14NTN Tinned Copper Braid

14"x1.64"x0.38"

By Burndy
Catalog # [B4E14NTN](#)

Tinned Copper Braid 14"x1.64"x0.38"



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	NC
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Dimension - Pad Width inch	1.64 in
----------------------------	---------

Length	14 in
Thickness	0.38 in
Dimension - Z inch	3.25 in
Dimension - L Length Overall mm	356 mm
Height	0.38 in
Width	1.64 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	14.00 in
Dimensions	14 in x 1.64 in x 0.38 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
UPC	781810442302
Material	Copper
Plating Type	Tin Plated
UPC 12 Digit	781810442302
UPC 14 Digit GTIN	00781810442302

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)