



B4E18G88TN Flexible Copper Braid

By Burndy
Catalog # B4E18G88TN

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	850 A
Rating - Outdoor Amperage	1020 A

Dimensions

Package Height	0.000 in
Length	18 in
Package Weight	0.000 lb.
Dimension - Width mm	42 mm
Dimension - Width inch	1.64
Package Length	0.000 in
Package Width	0.000 in
Height	0.38 in
Width	1.64 in
Dimension - Length Overall inch	12
Dimensions	18 in x 1.64 in x 0.38 in

General

Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	4
UPC	621945457218
Material	Copper
UPC 12 Digit	621945457218
UPC 14 Digit GTIN	00621945457218

Logistics

Minimum Pack Quantity	1
Pallet Quantity	480
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)