



# B4E20TN Flexible Copper Braid

By Burndy  
Catalog # B4E20TN

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

## Specifications

|                              |     |
|------------------------------|-----|
| Standards - RoHS Compliance  | CM  |
| Status                       |     |
| UL Listed                    | Yes |
| Certification - CSA Approved | Yes |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Dimensions

|                |           |
|----------------|-----------|
| Package Height | 0.000 in  |
| Length         | 20 in     |
| Package Weight | 0.000 lb. |
| Package Length | 0.000 in  |
| Package Width  | 0.000 in  |

## General

|                   |                |
|-------------------|----------------|
| UPC               | 621945452329   |
| Material          | Copper         |
| UPC 12 Digit      | 621945452329   |
| UPC 14 Digit GTIN | 00621945452329 |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 480 |
| Carton Quantity       | 5   |

## Product Assets

[Catalog \[English\]](#)