



B4E24D50N Flexible Copper Braid

By Burndy
Catalog # [B4E24D50N](#)

Flexible Copper Braid.

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B4E24D50N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810205174
UPC 14 Digit GTIN	00781810205174

Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	673.1 mm
Dimension - Length Overall inch	26.50 in
Dimension - Pad Width inch Length	1.64 in 24.5 in
Thickness	0.38 in

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	8
Minimum Pack Quantity	1
Pallet Quantity	720

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - B4E24D50N](#)



A Hubbell brand