



# B4E25G82TN Flexible Copper Braid

By Burndy  
Catalog # [B4E25G82TN](#)

Tin Plated Ferrules.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number                      B4E25G82TN

|                   |                |
|-------------------|----------------|
| Connector Type    | Braid          |
| Material          | Copper         |
| UPC               | 781810351062   |
| UPC 14 Digit GTIN | 00781810351062 |

### Dimensions

|        |       |
|--------|-------|
| Length | 25 in |
|--------|-------|

### Certifications And Compliance

|                             |    |
|-----------------------------|----|
| Standards - RoHS Compliance | EX |
| Status                      |    |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - B4E25G82TN](#)



A Hubbell brand