



# B4E35D50N Flexible Copper Braid

By Burndy  
Catalog # B4E35D50N

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                                    |     |
|------------------------------------|-----|
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Standards - RoHS Compliance Status | EX  |
| Certification - cULus              | No  |
| UL Listed                          | Yes |
| Certification - CSA Approved       | No  |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Dimensions

|                                 |           |
|---------------------------------|-----------|
| Dimension - Pad Width inch      | 1.64 in   |
| Package Height                  | 0.000 in  |
| Length                          | 35.5 in   |
| Thickness                       | 0.38 in   |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 901.7 mm  |
| Dimension - Hole Size inch      | 0.56 in   |
| Dimension - Length Overall inch | 35.50 in  |

## General

|                                       |                |
|---------------------------------------|----------------|
| Plated                                | Y              |
| Material - Ferrules                   | Y              |
| Physical Attribute - Number of Braids | 4              |
| UPC                                   | 781810205204   |
| Material                              | Copper         |
| UPC 12 Digit                          | 781810205204   |
| UPC 14 Digit GTIN                     | 00781810205204 |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 720 |
| Carton Quantity       | 8   |

## Product Assets

[Catalog \[English\]](#)