



B4E36N Flexible Copper Braid

36"x1.64"x0.38"

By Burndy
Catalog # B4E36N

Flexible Copper Braid 36"x1.64"x0.38"



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Dimension - Pad Width inch	1.64 in
Package Height	0.000 in
Length	36 in
Thickness	0.38 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	3.25 in
Dimension - L Length Overall mm	914 mm
Height	0.38 in
Width	1.64 in
Dimension - D inch	3.00 in
Dimension - N inch	0.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	36.00 in
Dimensions	36 in x 1.64 in x 0.38 in

General

Material - Ferrules	Y
Physical Attribute - Number of Braids	4
UPC	781810089378
Material	Copper
UPC 12 Digit	781810089378
UPC 14 Digit GTIN	00781810089378

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)