



B4EE38TNCG1 Flexible Copper Braid

By Burndy
Catalog # B4EE38TNCG1

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	1500 A
-----------------	--------

Rating - Outdoor Amperage	1500
---------------------------	------

Dimensions

Package Height	0.000 in
Length	38 in
Package Weight	0.000 lb.
Dimension - Width inch	2.75
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	965 mm
Weight	11.7 lb.
Dimension - Length Overall inch	38

General

Plated	Y
Material - Ferrules	Copper
Physical Attribute - Number of Braids	1
UPC	781810420997
Material	Copper
UPC 12 Digit	781810420997
UPC 14 Digit GTIN	00781810420997

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand