



B4F12NTN Flexible Copper Braid

By Burndy
Catalog # B4F12NTN

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Certification - CSA Approved Yes

Configuration

Connector Type Braid

Current

Rating - Indoor Amperage 1000 A
Rating - Outdoor Amperage 1200 A

Dimensions

Package Height	0.000 in
Length	12 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	305 mm
Dimension - Length Overall	12.00 inch

General

Plated	Y
Physical Attribute - Number of Braids	4
UPC	621945448179
Material	Copper
UPC 12 Digit	621945448179
UPC 14 Digit GTIN	00621945448179

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)