



B4F12NX90 Flexible Copper Braid

By Burndy
Catalog # [B4F12NX90](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:

www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance EX
Status
Certification - CSA Approved Yes

Configuration

Connector Type Braid

Dimensions

Length 12 in

General

UPC 781810257623
Material Copper
UPC 12 Digit 781810257623
UPC 14 Digit GTIN 00781810257623

Logistics

Minimum Pack Quantity 1
Pallet Quantity 900
Carton Quantity 10

Product Assets

[Catalog \[English\]](#)