



B4F12U Flexible Copper Braid

By Burndy
Catalog # B4F12U

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	1000 A
Rating - Outdoor Amperage	1200 A

Dimensions

Length	12 in
Dimension - L Length Overall	305 mm
mm	
Dimension - Length Overall	12.00 in
inch	

General

Plated	N
Material - Ferrules	Y
Physical Attribute - Number of	4
Braids	
UPC	781810280478
Material	Copper
UPC 12 Digit	781810280478
UPC 14 Digit GTIN	00781810280478

Product Assets

[Catalog \[English\]](#)