



B4F13G78TN Flexible Copper Braid

By Burndy
Catalog # [B4F13G78TN](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:

www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance CM
Status

Configuration

Connector Type Braid

Current

Rating - Indoor Amperage 1200 A

Rating - Outdoor Amperage 1000 A

Dimensions

Package Height 0.000 in
Length 13 in
Package Weight 0.000 lb.
Package Length 0.000 in
Package Width 0.000 in
Dimension - L Length Overall 330.2 mm
mm
Dimension - Length Overall 13 in
inch

General

UPC 781810474495
Material Copper
UPC 12 Digit 781810474495
UPC 14 Digit GTIN 00781810474495

Logistics

Minimum Pack Quantity 1
Pallet Quantity 900
Carton Quantity 10

Product Assets

[Catalog \[English\]](#)