



# B4F15 Flexible Copper Braid

By Burndy  
Catalog # B4F15

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                               |     |
|-------------------------------|-----|
| Certification - ETL           | No  |
| Certification - UL Recognized | No  |
| Standards - RoHS Compliance   | EX  |
| Status                        |     |
| Certification - cULus         | No  |
| UL Listed                     | Yes |
| Certification - CSA Approved  | No  |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Dimensions

|                                 |           |
|---------------------------------|-----------|
| Dimension - Pad Width inch      | 1.44 in   |
| Package Height                  | 0.000 in  |
| Length                          | 15 in     |
| Thickness                       | 0.88 in   |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 381 mm    |
| Dimension - Hole Size inch      | 0.44 in   |
| Dimension - Length Overall inch | 15.00 in  |

## General

|                                       |                |
|---------------------------------------|----------------|
| Plated                                | N              |
| Material - Ferrules                   | Y              |
| Physical Attribute - Number of Braids | 1              |
| UPC                                   | 781810127063   |
| Material                              | Copper         |
| UPC 12 Digit                          | 781810127063   |
| UPC 14 Digit GTIN                     | 00781810127063 |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Product Assets

[Catalog \[English\]](#)