



B4F28N Flexible Copper Braid

By Burndy
Catalog # B4F28N

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

General

Catalog Number	B4F28N
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
UPC	781810224748

UPC 14 Digit GTIN 00781810224748

Dimensions

Length 28 in

Electrical Ratings

Rating - Indoor Amperage	1000 A
Rating - Outdoor Amperage	1200 A

Certifications And Compliance

Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	1
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE212248-01](#)
[Specifications - B4F28N](#)



A Hubbell brand