



B4F72NB Flexible Copper Braid

By Burndy
Catalog # B4F72NB

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Certification - CSA Approved	Yes
UL Listed	Yes
Standards - RoHS Compliance Status	CM

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	1000 A
Rating - Outdoor Amperage	1200 A

Dimensions

Dimension - L Length Overall mm	1829
Dimension - Length Overall inch	72.00 in
Weight	35.47 lb.
Length	72 in

General

Insulation	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Material	Copper
UPC	621945467897

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	35

Product Assets

[Catalog \[English\]](#)