



B4G47D3NTN Flexible Copper Braid

By Burndy
Catalog # B4G47D3NTN

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance NC
Status

Configuration

Connector Type Braid

Current

Rating - Indoor Amperage 1200
Rating - Outdoor Amperage 1440

Dimensions

Length 47.3 in
Dimension - L Length Overall 1201 mm
mm
Dimension - Length Overall 47.30 in
inch

General

Plated Y
Material - Ferrules Y
Physical Attribute - Number of Braids 4
UPC 781810444658
Material Copper
UPC 12 Digit 781810444658
UPC 14 Digit GTIN 00781810444658

Logistics

Pallet Quantity 1080
Carton Quantity 12

Product Assets

[Catalog \[English\]](#)