



B4G8N Flexible Copper Braid

By Burndy
Catalog # B4G8N

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No

UL Listed	Yes
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Length	8 in
--------	------

General

UPC	781810287743
Material	Copper
UPC 12 Digit	781810287743
UPC 14 Digit GTIN	00781810287743

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1080
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)