



BURNDY

B773436L1320 Flexible copper braid 1320.00"x0.30

By Burndy

Catalog # [B773436L1320](#)

Flexible copper braid 1320.00"x0.30



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Certification - ETL

No
Certification - UL Recognized
No
Standards - RoHS Compliance Status
UI
Certification - cULus
No
UL Listed
No
Certification - CSA Approved
No

Configuration

Connector Type
Braid

Dimensions

Length
1320 in
Dimension - Width inch
0.3
Dimension - L Length Overall mm
33528
Width
0.3 in
Dimension - Length Overall inch
1320

General

UPC
781810507063
Material
Copper
UPC 12 Digit
781810507063
UPC 14 Digit GTIN
00781810507063

Logistics

Minimum Pack Quantity
1
Pallet Quantity
1
Carton Quantity
1

Product Assets

[Catalog.\[English\]](#)



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRDY-B773436L1320-SPEC-EN | REV 5/2026