



B775936L3960 Flexible tinned copper braid 3960.00"x0.40"

By Burndy
Catalog # B775936L3960

Flexible tinned copper braid 3960.00"x0.40"



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	UI
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size #36 AWG

Configuration

Connector Type Braid

Dimensions

Length	3960 in
Dimension - Width mm	10 mm
Dimension - Width inch	0.40
Dimension - L Length Overall mm	100584
Dimension - Length Overall inch	3960.00

General

Physical Attribute - Number of Braids	1
UPC	781810658284
Material	Copper
UPC 12 Digit	781810658284
UPC 14 Digit GTIN	00781810658284

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalog \[English\]](#)