



BA10E14, Vinyl Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [BA10E14](#)



Vinyl Ring Terminal For 12 - 10 AWG

Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

Application

For Commercial, Light Duty Industrial Control and Power Circuit Applications

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor - Copper Str Size	12 AWG 10 AWG

Configuration

Physical Attribute - Number of Holes 1

Connector Type

Ring Terminal

Dimensions

Dimension - Pad Width inch	0.53 in
Package Height	0.000 in
Dimension - Hole Size fraction	10/37
Dimension - Bolt Size fraction	1/4
Length	1.22 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.40 in
Height	0.54 in
Width	0.54 in
Dimension - Hole Size inch	0.27 in
Dimension - Length Overall inch	1.22 in
Dimension - Stud Size inch	1/4
Dimensions	1.22 in x 0.54 in x 0.54 in

General

Feature - Barrel Style	Shrouded
Plated	Y
Insulation Type	Vinyl
Trade Name	VINYLUG™
Physical Attribute - Tongue Type	Ring
Sub Brand	VINYLUG
UPC	781810026472
Type	Ring Tongue
Insulation	Y
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810026472
UPC 14 Digit GTIN	00781810026472

Logistics

Pallet Quantity	99999
Carton Quantity	500

Product Assets

[Catalog \[English\]](#)



A Hubbell brand