



BA10E38, Vinyl Ring Terminal For 12 - 10 AWG

By Burndy

Catalog # [BA10E38](#)

Vinyl Ring Terminal For 12 - 10 AWG



Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

Application

For Commercial, Light Duty Industrial Control and Power Circuit Applications

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer
EU RoHS Indicator	No
Certification - UL Recognized	Yes
Industry Standard(s)	No
Buy America(n) Qualified	UL467
Certification - ETL	Contact Manufacturer
Standards - Industry Standards Met	No
Standards - RoHS Compliance Status	UL486
Certification - CSA Approved	CM
UL Listed	Yes

Conductor

Conductor - Copper Str Size	12 AWG 10 AWG
Conductor Size	12 - 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---



A Hubbell brand

Connector Type

Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Pad Width inch	0.53 in
Package Height	0.000 in
Dimension - Hole Size fraction	16/41
Dimension - Hole Size inch	0.39 in
Dimension - Stud Size inch	3/8
Width	0.54 in
Dimension - Z inch	0.45 in
Length	1.27 in
Dimension - Bolt Size fraction	3/8
Dimension - Length Overall inch	1.27 in
Height	0.54 in
Dimensions	1.27 in x 0.54 in x 0.54 in

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Sub Brand	VINYLUG
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Style	Shrouded
Type	Ring Tongue
UPC 12 Digit	781810026489
UPC 14 Digit GTIN	00781810026489
Material	Copper
Plating Type	Tin
UPC	781810026489

Logistics

Minimum Pack Quantity	500
Carton Quantity	500
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)