



BA10E38M, Vinyl Ring Terminal For 12 - 10 AWG (Tape Mounted)

By Burndy
Catalog # [BA10E38M](#)



Vinyl Ring Terminal For 12 - 10 AWG (Tape Mounted)

Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

Specifications

Certification - CSA Approved	Yes
UL Listed	Yes
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM

Conductor

Conductor Size	12 - 10 AWG
Configuration	
Connector Type	Ring Terminal
Dimensions	
Width	0.54 in
Height	0.54 in
Length	1.27 in
Dimension - Bolt Size fraction	3/8
Dimensions	1.27 in x 0.54 in x 0.54 in

General

Type	Ring Tongue
Material	Copper
UPC	781810028889
Insulation Type	Vinyl
Trade Name	VINYLUG™

Logistics

Minimum Pack Quantity	1000
-----------------------	------

Product Assets

[Catalog \[English\]](#)