

BA10E516, Vinyl Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [BA10E516](#)



Vinyl Ring Terminal For 12 - 10 AWG

Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	12 AWG 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Z inch	0.40 in
Dimension - Pad Width inch	0.53 in
Package Height	0.000 in
Length	1.27 in
Dimension - Hole Size fraction	1/3
Dimension - Bolt Size fraction	5/16
Dimension - Hole Size inch	0.33 in
Dimension - Stud Size inch	5/16
Dimension - Length Overall inch	1.22 in
Width	0.54 in
Height	0.54 in
Dimensions	1.27 in x 0.54 in x 0.54 in

General

Insulation Type	Vinyl
Physical Attribute - Tongue Type	Ring
Trade Name	VINY LUG™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation	Y
Type	Ring Tongue
UPC 12 Digit	781810026496
UPC 14 Digit GTIN	00781810026496
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810026496

Logistics

Minimum Pack Quantity	500
Carton Quantity	500
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)