

BA10EL6, Vinyl Locking Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [BA10EL6](#)

Vinyl Locking Fork Terminal For 12 - 10 AWG



Features

- Locking Fork Tongue design
- Allows for fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking form is made from copper alloy and permits many installations while maintaining proper spring retention of forks

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Locking Fork Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in

Package Weight	0.000 lb.
Dimension - Z inch	0.26 in
Dimension - Pad Width inch	0.28 in
Package Height	0.000 in
Length	1.05 in
Dimension - Hole Size fraction	7/50
Dimension - Bolt Size fraction	#6
Dimension - Hole Size inch	0.14 in
Dimension - Stud Size inch	#6
Dimension - Length Overall inch	1.05 in
Width	0.29 in
Height	0.29 in
Dimensions	1.05 in x 0.29 in x 0.29 in

General

Insulation Type	Vinyl
Physical Attribute - Tongue Type	Locking Fork
Trade Name	VINYLUG™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation	Y
UPC 12 Digit	781810026885
UPC 14 Digit GTIN	00781810026885
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810026885

Logistics

Minimum Pack Quantity	500
Carton Quantity	500
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)