

BA10EZ10, Vinyl Flanged Fork Terminal, 12-10 AWG, #10 Stud

By Burndy
Catalog # [BA10EZ10](#)



Vinyl Insulated Copper Flanged Fork Terminal For 12 - 10 AWG, #10 Stud, Bulk Packaged

Features

- Locking Fork Tongue design
- Allows for fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking form is made from copper alloy and permits many installations while maintaining proper spring retention of forks

Application

For Fast Installation And Security

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	12 AWG-10 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Flanged Fork Terminal

Dimensions

Dimension - Pad Width inch	0.41 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/5
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Width	0.41 in
Dimension - Hole Size inch	0.20 in
Dimension - Stud Size inch	#10
Dimension - Bolt Size fraction	#10
Length	1.09 in
Dimension - Z inch	0.31 in
Height	0.41 in
Dimension - Length Overall inch	1.09 in
Dimensions	1.09 in x 0.41 in x 0.41 in

General

Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Yes
Physical Attribute - Tongue Type	Flanged Fork
Sub Brand	VINYLUG
Product Type	Terminal
UPC	781810026441
Type	Flange Fork
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810026441
UPC 14 Digit GTIN	00781810026441

Logistics

Minimum Pack Quantity	10000
Pallet Quantity	99999
Carton Quantity	500

Product Assets

[Catalog \[English\]](#)