



BA14EF2, Vinyl Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [BA14EF2](#)



Vinyl Fork Terminal For 16 - 14 AWG

Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	16 AWG 14 AWG
Conductor - Copper Solid Size	16 AWG 15 AWG 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG

Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Pad Width inch	0.17 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/11
Dimension - Hole Size inch	0.09 in
Dimension - Stud Size inch	#2
Width	0.18 in
Dimension - Z inch	0.23 in
Length	0.75 in
Dimension - Bolt Size fraction	#2
Dimension - Length Overall inch	0.75 in
Height	0.18 in
Dimensions	0.75 in x 0.18 in x 0.18 in

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Sub Brand	VINYLUG
Physical Attribute - Tongue Type	Fork
Plated	Y
Feature - Barrel Style	Shrouded
Type	BA-EF
UPC 12 Digit	781810026434
UPC 14 Digit GTIN	00781810026434
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810026434

Logistics

Minimum Pack Quantity	1
-----------------------	---

Carton Quantity1000

Pallet Quantity99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand