

BA14EL8M, Vinyl Lock Fork Term, 16 - 14 AWG (Tape Mounted)

By Burndy
Catalog # [BA14EL8M](#)



Tape Mounted, Vinyl Insulated Copper Locking Fork Terminal For 16 - 14 AWG, #8 Stud

Features

- Vinyl Locking Fork Tongue Terminals banded together on mylar carrier strip for high volume crimping
- Meets IEA-468-B standard
- Can be integrated with fully autonomous wire harness machines

Application

Terminal - Fork

Specifications

Certification - UL Recognized	N
Buy American Compliant	No
Certification - cULus	N
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Solid Size	• 16 AWG • 15 AWG • 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	16 AWG - 14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Locking Fork Terminal

Dimensions

Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	8/47
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Width	0.32 in
Dimension - Thread Size	-
Dimension - Hole Size inch	0.17 in
Dimension - Stud Size inch	#8
Dimension - Bolt Size fraction	#8
Length	0.91 in
Dimension - Z inch	0.26 in
Height	0.32 in
Dimension - Length Overall inch	0.91 in
Dimensions	0.91 in x 0.32 in x 0.32 in

General

Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Yes
Physical Attribute - Tongue Type	Locking Fork
Sub Brand	VINYLUG
Product Type	Terminal
UPC	781810029350
Type	Small Terminals
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810029350
UPC 14 Digit GTIN	00781810029350

Logistics

Minimum Pack Quantity	2000
-----------------------	------

Product Assets

[Catalog \[English\]](#)