



BA16E8M, Vinyl Ring Terminal For 22 - 16 AWG (Tape Mounted)

By Burndy
Catalog # [BA16E8M](#)



Vinyl Ring Terminal For 22 - 16 AWG (Tape Mounted)

Features

- Vinyl Ring Tongue Terminals banded together on mylar carrier strip for high volume crimping
- Meets IEA-468-B standard
- Can be integrated with fully autonomous wire harness machines

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Solid Size Range	• 20 AWG -22 AWG • 16 AWG -18 AWG
Conductor Size	22 - 16 AWG
Conductor - Copper Str Size Range	• 20 AWG - 22 AWG • 16 AWG - 18 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Z inch	0.26 in
Dimension - Pad Width inch	0.31 in
Length	0.85 in
Dimension - Hole Size fraction	8/47
Dimension - Bolt Size fraction	#8
Dimension - Hole Size inch	0.17 in
Dimension - Stud Size inch	#8
Dimension - Length Overall inch	0.85 in
Width	0.32 in
Height	0.32 in
Dimensions	0.85 in x 0.32 in x 0.32 in

General

Insulation Type	Vinyl
Physical Attribute - Tongue Type	Ring
Trade Name	VINYLUG™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation Type	Y
Type	Ring Tongue
UPC 12 Digit	781810029077
UPC 14 Digit GTIN	00781810029077
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810029077

Logistics

Minimum Pack Quantity	2000
-----------------------	------

Product Assets

[Catalog \[English\]](#)