

BA16EL10, Vinyl Locking Fork Terminal, 22-16 AWG, #10 Stud

By Burndy
Catalog # [BA16EL10](#)



Vinyl Insulated Copper Locking Fork Terminal For 22 - 16 AWG, #10 Stud, Bulk Packaged

Features

- Locking Fork Tongue design
- Allows for fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking form is made from copper alloy and permits many installations while maintaining proper spring retention of forks

Application

For Fast Installation And Security

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	22 - 16 AWG
Conductor - Copper Solid Size Range	• 20 AWG -22 AWG • 16 AWG -18 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	• 20 AWG - 22 AWG • 16 AWG - 18 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Locking Fork Terminal

Dimensions

Dimension - Pad Width inch	0.36 in
----------------------------	---------

Package Height	0.000 in
Dimension - Hole Size fraction	15/79
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Width	0.37 in
Dimension - Hole Size inch	0.19 in
Dimension - Stud Size inch	#10
Dimension - Bolt Size fraction	#10
Length	1.02 in
Dimension - Z inch	0.31 in
Height	0.37 in
Dimension - Length Overall inch	1.02 in
Dimensions	1.02 in x 0.37 in x 0.37 in

General

Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Yes
Physical Attribute - Tongue Type	Locking Fork
Sub Brand	VINYLUG
Product Type	Terminal
UPC	781810026960
Type	BA-EL, Locking
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810026960
UPC 14 Digit GTIN	00781810026960

Logistics

Pallet Quantity	99999
Carton Quantity	1000

Product Assets

[Catalog \[English\]](#)