



BB019ML24T14TN, One-Hole Braid, 24" long, 1/4" stud, tin plated

By Burndy
Catalog # [BB019ML24T14TN](#)

One-Hole Braid, 19 kcmil, 24", 1/4" stud, tin plated

Features

- Most Burndy braid are UL Listed and CSA Certified
 - Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
 - Braid is especially suited for applications that require flexibility or resistance to vibration
 - Extra fine stranding gives enhanced flexibility
 - Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
 - Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
 - For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
- www.hubbell.com/config/BRAID

Conductor



Conductor Size	#8 AWG
Wire Size	10mm2

Dimensions

Width	0.39 in
Length	24 in
Thickness	0.08 in
Dimension - Stud Size inch	1/4"

General

UPC	621945650367
-----	--------------

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)